

# Eaton 10250ED1277-3

Catalog Number: 10250ED1277-3

Toggle Switch, Commercial, Ivory, Screw, Wall, Four-way, Copper alloy, 120/277 Vac, #14-10 AWG, Side wire, 0.031 in-10250ED1277-3

## General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250ED1277-3
UPC	Product Length/Depth
782116323005	1 in
Product Height	Product Width
1 in	1 in
Product Weight	Warranty
0.1 lb	1 year
Compliances	Certifications
CE Marked	UL Listed
	CSA Certified



## Product specifications

### Product Category

Selector switch

### Throw type

60 °

### Number of positions

2

### Series

10250T

### Type

30.5 mm, Heavy-Duty

### Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

### Illumination

Non-illuminated

### Cam code

Cam 1

### Key removal position

Right and left

### Actuator

Key

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250ED1277-3



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia