

# Eaton 10250ED1309-3

Catalog Number: 10250ED1309-3

Eaton 10250T pushbutton, 10250T, 30.5 mm, Heavy-Duty, 40 mm, Low temperature diaphragm, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Momentary, Mushroom, Red actuator, T1 and T2, Chrome bezel, Plastic actuator

## General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250ED1309-3
UPC	Product Length/Depth
782116323173	1 in
Product Height	Product Width
1 in	1 in
Product Diameter	Product Weight
2.5 in	0.1 lb
Warranty	Compliances
1 year	CE Marked
Certifications	
UL Listed	
CSA Certified	

## Product specifications

### Contact configuration

T2

T1

### Special features

Low temperature diaphragm

### Actuator color

Red

### Bus material

Zinc die cast

### Actuator material

Plastic

### Rating

NEMA 12

NEMA 3R

NEMA 4X

NEMA 3

NEMA 13

NEMA 4

### Size

40 mm

### Bezel

Chrome

### Series

10250T

### Type

Pushbutton

### Operating mode

Momentary

### Illumination

Non-illuminated

### Actuator

Mushroom

### Degree of protection

NEMA 13

NEMA 12

NEMA 3

NEMA 4

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250ED1309-3

NEMA 4X

NEMA 3R



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)