

# Eaton 10250H2538

Catalog Number: 10250H2538

Eaton 10250T pushbutton,10250H, Assembled control station, 30.5 mm, Heavy-Duty, NEMA 1, Black, Three-position selector switch, knob, Open type (no cover), RUN/OFF/AUTO, Horizontal/vertical, One element

## General specifications

### Product Name

Eaton 10250T pushbutton

### Catalog Number

10250H2538

### UPC

782113223001

### Product Length/Depth

2.25 in

### Product Height

2.63 in

### Product Width

4.25 in

### Product Weight

1 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

CE Marked

### Certifications

CSA Certified  
UL 505

### Catalog Notes

Open type enclosure.



## Product specifications

### Product category

Assembled control station

### Series

10250H

### Type

30.5 mm, Heavy-Duty

### Actuator color

Black

### Legend

RUN OFF AUTO

### Number of elements

1

### Illumination

PresTest

### Enclosure

NEMA 1 (open type, no cover)

### Mounting method

Vertical

Horizontal

### Actuator

Three position selector switch, knob

### Degree of protection

NEMA 3R

NEMA 3

NEMA 13

NEMA 4

NEMA 12

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250H2538



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)