

Eaton 10250H2740

Catalog Number: 10250H2740

Eaton 10250T pushbutton,10250H, Assembled control station, 30.5 mm, Heavy-Duty, NEMA 3, 3R, 4, 4X, 13, Mechanically interlocked, Die cast, FOR/REV, Horizontal/vertical, Two element

General specifications

Product Name

Eaton 10250T pushbutton

Catalog Number

10250H2740

UPC

782113223070

Product Length/Depth

7.9 in

Product Height

5 in

Product Width

4 in

Product Weight

1.8 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

CE Marked

Certifications

UL 505

CSA Certified

Catalog Notes

No legend on button. Specify any Standard legend, no price change. Open type enclosure. Round button.



Product specifications

Enclosure material

Die cast

Product category

Assembled control station

Series

10250H

Type

30.5 mm, Heavy-Duty

Legend

FOR REV

Number of elements

2

Illumination

PresTest

Enclosure

NEMA 4

NEMA 3R

NEMA 4X

NEMA 3

NEMA 13

Mounting method

Vertical

Horizontal

Actuator

Mechanically interlocked

Degree of protection

NEMA 3R

NEMA 13

NEMA 12

NEMA 4

NEMA 3

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250H2740

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)