

Eaton 10250T1063LGD06-1X

Catalog Number: 10250T1063LGD06-1X

Eaton 30.5 mm Heavy-Duty Push-Pull, Assembled, Standard 40 mm Actuator (Lens), Green, 1NO-1NC, Bayonet base, Illuminated, 6 Vac/Vdc Lamp, LED, transformer, 120 Vac Light Unit, Three-position, Mom. Push/pull, Main. intermediate, 10250T Series

General specifications

| | |
|----------------------------|----------------------|
| Product Name | Catalog Number |
| Eaton 10250T pushbutton | 10250T1063LGD06-1X |
| UPC | Product Length/Depth |
| 782114714751 | 1 in |
| Product Height | Product Width |
| 1 in | 1 in |
| Product Diameter | Product Weight |
| 2.63 in | 0.1 lb |
| Warranty | Compliances |
| 1 year | CE Marked |
| Certifications | Catalog Notes |
| UL Listed CSA Certified | Assembled at Factory |



Product specifications

Contact configuration

1 NO-1 NC

Special features

Factory Assembled

Number of positions

3

Actuator color

Green

Bus material

Plastic

Light unit voltage

120 Vac

Lamp voltage - min

6 V

Rating

NEMA 3R

NEMA 13

NEMA 4

NEMA 3

NEMA 4X

NEMA 12

NEC Class I Division 2, Groups B, C and D

Size

40 mm

Series

10250T

Lamp voltage - max

6 V

Light unit type

LED, transformer

Type

Class I Division 2

Operating mode

Push: momentary

Pull: momentary

Intermediate: maintained

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T1063LGD06-1X

Illumination

Illuminated

Actuator

Standard



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)