

# Eaton 10250T1097LED24-1X

Catalog Number: 10250T1097LED24-1X

Eaton 10250T pushbutton, 30.5 mm, Heavy-Duty, 40 mm, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, Three-position, Momentary push and pull, Standard, Red actuator, Plastic bus, LED, 1NO-1NC, 24 Vac/dc LUV, 24 Vac/dc lamp

## General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T1097LED24-1X
UPC	Product Length/Depth
782114714201	5 in
Product Height	Product Width
2 in	2 in
Product Weight	Warranty
0.4 lb	1 year
Compliances	Certifications
CE Marked	UL Listed
	CSA Certified
Catalog Notes	
Assembled at Factory	



## Product specifications

### Contact configuration

1 NO-1 NC

### Number of positions

3

### Actuator color

Red

### Legend

EMERGENCY STOP

### Bus material

Plastic

### Light unit voltage

24 Vac/dc

### Lamp voltage - min

24 V

### Rating

NEMA 3R

NEMA 12

NEMA 4X

NEMA 3

NEMA 13

NEMA 4

### Size

40 mm

### Series

10250T

### Lamp voltage - max

24 V

### Light unit type

LED, full voltage

### Type

30.5 mm, Heavy-Duty

### Operating mode

Pull: momentary

Push: momentary

### Illumination

Illuminated

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250T1097LED24-1X

Actuator  
Standard

---



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)