

Eaton 10250T1311-X3

Catalog Number: 10250T1311-X3

Eaton 10250T pushbutton, 10250T, Selector switch, 30.5 mm, Metal, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Two-position, Knob, Black actuator, Chrome bezel, Vertical

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T1311-X3
UPC	Product Length/Depth
782113936130	1 in
Product Height	Product Width
1 in	1 in
Product Diameter	Product Weight
1.38 in	0.1 lb
Warranty	Compliances
1 year	CE Marked
Certifications	Catalog Notes
CSA Certified UL Listed	Field convertible to Horizontal Mounting or order operator only and separate operator cap.



Product specifications

Product Category

Selector switch

Throw type

60 °

Series

10250T

Number of positions

2

Type

30.5 mm, metallic

Actuator color

Black

Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

Illumination

Non-illuminated

Mounting method

Vertical

Bezel

Chrome

Actuator

Knob

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T1311-X3



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia