

# Eaton 10250T1323-123

Catalog Number: 10250T1323-123

Eaton 10250T pushbutton, 10250T, Selector switch, 30.5 mm, Metal, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Three-position, Knob, Black actuator, Vertical, 3NO-3NC, Chrome bezel

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton 10250T pushbutton	10250T1323-123
<b>UPC</b>	<b>Product Length/Depth</b>
782113950679	1 in
<b>Product Height</b>	<b>Product Width</b>
1 in	1 in
<b>Product Diameter</b>	<b>Product Weight</b>
1.38 in	0.1 lb
<b>Warranty</b>	<b>Compliances</b>
1 year	CE Marked
<b>Certifications</b>	<b>Catalog Notes</b>
UL Listed CSA Certified	Field convertible to Horizontal Mounting or order operator only and separate operator cap.



## Product specifications

### Product Category

Selector switch

### Contact configuration

3 NO-3 NC

### Throw type

60 °

### Series

10250T

### Number of positions

3

### Type

30.5 mm, metallic

### Actuator color

Black

### Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

### Illumination

Non-illuminated

### Mounting method

Vertical

### Bezel

Chrome

### Actuator

Knob

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250T1323-123