

# Eaton 10250T1343-Y2

Catalog Number: 10250T1343-Y2

Eaton 10250T pushbutton, 10250T, Selector switch, 30.5 mm, Metal, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Three-position, Knob, Black actuator, Chrome bezel

## General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T1343-Y2
UPC	Product Length/Depth
782113936444	1 in
Product Height	Product Width
1 in	1 in
Product Diameter	Product Weight
1.38 in	0.1 lb
Warranty	Compliances
1 year	CE Marked
Certifications	
CSA Certified	
UL Listed	

## Product specifications

### Product Category

Selector switch

### Throw type

60 °

### Series

10250T

### Number of positions

3

### Type

30.5 mm, metallic

### Actuator color

Black

### Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

### Illumination

Non-illuminated

### Bezel

Chrome

### Actuator

Knob

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250T1343-Y2



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia