

Eaton 10250T15112-11X

Catalog Number: 10250T15112-11X

Eaton 10250T pushbutton, 10250T, Selector switch, 30.5 mm, Heavy-Duty, Cam 1, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Two-position, Key, Vertical, 2 NO-2 NC, Left only

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T15112-11X
UPC	Product Length/Depth
782113752402	1 in
Product Height	Product Width
1 in	1 in
Product Diameter	Product Weight
1.38 in	0.1 lb
Warranty	Compliances
1 year	CE Marked
Certifications	
CSA Certified	
UL Listed	



Product specifications

Product Category

Selector switch

Contact configuration

2 NO-2 NC

Throw type

60 °

Series

10250T

Number of positions

2

Type

30.5 mm, Heavy-Duty

Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

Illumination

Non-illuminated

Cam code

Cam 1

Mounting method

Vertical

Key removal position

Left only

Actuator

Key

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T15112-11X