

Eaton 10250T15112

Catalog Number: 10250T15112

Eaton 10250T, Selector switch, 30.5 mm, Heavy-Duty, Cam 1, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Two-position, Key, Left only

General specifications

| | |
|-------------------------|----------------------------|
| Product Name | Catalog Number |
| Eaton 10250T pushbutton | 10250T15112 |
| UPC | Product Length/Depth |
| 782113227481 | 1.9 in |
| Product Height | Product Width |
| 2.2 in | 2 in |
| Product Weight | Warranty |
| 0.35 lb | 1 year |
| Compliances | Certifications |
| CE Marked | UL Listed CSA Certified |



Product specifications

Product Category

Selector switch

Throw type

60 °

Number of positions

2

Series

10250T

Type

30.5 mm, Heavy-Duty

Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

Illumination

Non-illuminated

Cam code

Cam 1

Key removal position

Left only

Actuator

Key operated

Resources

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Multimedia

[How to size and select a Power Supply](#)

Specifications and datasheets

[Eaton Specification Sheet - 10250T15112](#)

[Cam selection for pushbutton selectors](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)