

Eaton 10250T15112H620

Catalog Number: 10250T15112H620

Eaton 10250T pushbutton, Key, Chrome, Cam 1, Non-illuminated, H620, Left only, Maintained Two-position, Selector switch, NEMA 3, 3R, 4, 4X, 12, 13, 10250T, 60°

General specifications

| | |
|-------------------------|----------------------|
| Product Name | Catalog Number |
| Eaton 10250T pushbutton | 10250T15112H620 |
| UPC | Product Length/Depth |
| 782114000595 | 2.5 in |
| Product Height | Product Width |
| 1.75 in | 1.75 in |
| Product Weight | Warranty |
| 0.39 lb | 1 year |
| Compliances | Certifications |
| CE Marked | CSA Certified |
| | UL Listed |

Product specifications

Product Category

Selector switch

Throw type

60 °

Number of positions

2

Series

10250T

Type

Pushbutton

Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

Illumination

Non-illuminated

Cam code

Cam 1

Key removal position

Left only

Bezel

Chrome

Actuator

Key

Key code

H620

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Cam selection for pushbutton selectors

Eaton Specification Sheet - 10250T15112H620