

# Eaton 10250T15112H654-1

Catalog Number: 10250T15112H654-1

10250T, Selector switch, 30.5 mm, Heavy-Duty, Cam 1, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Two-position, Key, Vertical, 1NO-1NC, Left only, H654, Chrome bezel

## General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T15112H654-1
UPC	Product Length/Depth
782113500812	2.5 in
Product Height	Product Width
1.75 in	1.75 in
Product Weight	Warranty
0.39 lb	1 year
Compliances	Certifications
CE Marked	UL Listed
	CSA Certified

## Catalog Notes

With H Series Lock and Key Code: H654



## Product specifications

### Product Category

Selector switch

### Throw type

60 °

### Contact configuration

1 NO-1 NC

### Number of positions

2

### Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

### Mounting method

Vertical

### Bezel

Chrome

### Key code

H654

### Series

10250T

### Type

Pushbutton

### Illumination

Non-illuminated

### Cam code

Cam 1

### Key removal position

Left only

### Actuator

Key

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250T15112H654-1



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)