

Eaton 10250T15112H675

Catalog Number: 10250T15112H675

10250T, Selector switch, 30.5 mm, Metal, Cam 1, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Two-position, Key, Left only, H675, Chrome bezel

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T15112H675
UPC	Product Length/Depth
782114958957	2.5 in
Product Height	Product Width
1.75 in	1.75 in
Product Weight	Warranty
0.39 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified
	UL Listed



Product specifications

Product Category

Selector switch

Throw type

60 °

Number of positions

2

Series

10250T

Type

Pushbutton

Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

Illumination

Non-illuminated

Cam code

Cam 1

Key removal position

Left only

Bezel

Chrome

Actuator

Key

Key code

H675

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T15112H675

Cam selection for pushbutton selectors