

# Eaton 10250T15112H774

Catalog Number: 10250T15112H774

10250T, Selector switch, 30.5 mm, Metal, Cam 1, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Two-position, Maintained, Key, Left only, H774

## General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T15112H774
UPC	Product Length/Depth
782116076987	2.5 in
Product Height	Product Width
1.75 in	1.75 in
Product Weight	Warranty
0.39 lb	1 year
Compliances	Certifications
CE Marked	UL Listed
	CSA Certified



## Product specifications

### Product Category

Selector switch

### Throw type

60 °

### Number of positions

2

### Series

10250T

### Type

Pushbutton

### Operating mode

Maintained

### Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

### Illumination

Non-illuminated

### Cam code

Cam 1

### Key removal position

Left only

### Actuator

Key

### Key code

H774

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Cam selection for pushbutton selectors

Eaton Specification Sheet - 10250T15112H774