

# Eaton 10250T15112MD13

Catalog Number: 10250T15112MD13

Eaton 30.5 mm, Heavy-Duty Selector Switch Operator 10250T, 30.5 mm, Heavy-Duty, Lock with master key, Cam 1, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Two-position, Key, Left only, MD13

## General specifications

|                         |                      |
|-------------------------|----------------------|
| Product Name            | Catalog Number       |
| Eaton 10250T pushbutton | 10250T15112MD13      |
| UPC                     | Product Length/Depth |
| 782114347621            | 2.5 in               |
| Product Height          | Product Width        |
| 2 in                    | 2 in                 |
| Product Weight          | Warranty             |
| 0.4 lb                  | 1 year               |
| Compliances             | Certifications       |
| CE Marked               | UL Listed            |
|                         | CSA Certified        |



## Product specifications

### Throw type

60 °

### Special features

Lock with master key

### Number of positions

2

### Series

10250T

### Type

30.5 mm, Heavy-Duty

### Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

### Illumination

Non-illuminated

### Cam code

Cam 1

### Key removal position

Left only

### Actuator

Key operated

### Key code

MD13

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250T15112MD13

Cam selection for pushbutton selectors



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia