

# Eaton 10250T15112MD9

Catalog Number: 10250T15112MD9

Eaton 30.5 mm, Heavy-Duty Watertight/Oiltight, Selector Switch 10250T, 30.5 mm, Metal, Cam 1, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Two-position, Key, Left only, MD9, Chrome bezel

## General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T15112MD9
UPC	Product Length/Depth
782114000878	2.5 in
Product Height	Product Width
2 in	2 in
Product Weight	Warranty
0.4 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified
	UL Listed



## Product specifications

### Throw type

60 °

### Number of positions

2

### Series

10250T

### Type

30.5 mm, metallic

### Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

### Illumination

Non-illuminated

### Cam code

Cam 1

### Key removal position

Left only

### Bezel

Chrome

### Actuator

Key operated

### Key code

MD9

## Resources

### Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

### Multimedia

[How to size and select a Power Supply](#)

### Specifications and datasheets

[Cam selection for pushbutton selectors](#)

[Eaton Specification Sheet - 10250T15112MD9](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)