

Eaton 10250T15113MD14

Catalog Number: 10250T15113MD14

Eaton 10250T pushbutton, 10250T, 30.5 mm, Metal, Cam 1, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Two-position, Key, Right and left, MD14, Chrome bezel

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T15113MD14
UPC	Product Length/Depth
782114959190	1 in
Product Height	Product Width
1 in	1 in
Product Diameter	Product Weight
1.38 in	0.1 lb
Warranty	Compliances
1 year	CE Marked
Certifications	
CSA Certified	
UL Listed	



Product specifications

Throw type

60 °

Series

10250T

Number of positions

2

Type

30.5 mm, metallic

Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

Illumination

Non-illuminated

Cam code

Cam 1

Key removal position

Right and left

Bezel

Chrome

Actuator

Key

Key code

MD14

Resources

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Multimedia

[How to size and select a Power Supply](#)

Specifications and datasheets

[Eaton Specification Sheet - 10250T15113MD14](#)

[Cam selection for pushbutton selectors](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)