

# Eaton 10250T15113ME11

Catalog Number: 10250T15113ME11

Eaton 10250T pushbutton, 10250T, 30.5 mm, Metal, Cam 1, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Two-position, Key, Right and left, ME11, Chrome bezel

## General specifications

|                         |                      |
|-------------------------|----------------------|
| Product Name            | Catalog Number       |
| Eaton 10250T pushbutton | 10250T15113ME11      |
| UPC                     | Product Length/Depth |
| 782114959299            | 1 in                 |
| Product Height          | Product Width        |
| 1 in                    | 1 in                 |
| Product Diameter        | Product Weight       |
| 1.38 in                 | 0.1 lb               |
| Warranty                | Compliances          |
| 1 year                  | CE Marked            |
| Certifications          |                      |
| CSA Certified           |                      |
| UL Listed               |                      |



## Product specifications

### Throw type

60 °

### Series

10250T

### Number of positions

2

### Type

30.5 mm, metallic

### Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

### Illumination

Non-illuminated

### Cam code

Cam 1

### Key removal position

Right and left

### Bezel

Chrome

### Actuator

Key

### Key code

ME11

## Resources

### Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

### Multimedia

[How to size and select a Power Supply](#)

### Specifications and datasheets

[Eaton Specification Sheet - 10250T15113ME11](#)

[Cam selection for pushbutton selectors](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)