

# Eaton 10250T15236

Catalog Number: 10250T15236

Eaton 30.5 mm, Heavy-Duty Selector Switch Operator 10250T, Selector switch, 30.5 mm, Heavy-Duty, Cam 3, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Three-position, Key, Left and center

## General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T15236
UPC	Product Length/Depth
782113456935	2 in
Product Height	Product Width
2.5 in	2 in
Product Weight	Warranty
0.396 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified
	UL Listed



## Product specifications

### Product Category

Selector switch

### Throw type

60 °

### Number of positions

3

### Series

10250T

### Type

30.5 mm, Heavy-Duty

### Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

### Illumination

Non-illuminated

### Cam code

Cam 3

### Key removal position

Left and center

### Actuator

Key operated

## Resources

### Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

### Multimedia

[How to size and select a Power Supply](#)

### Specifications and datasheets

[Cam selection for pushbutton selectors](#)

[Eaton Specification Sheet - 10250T15236](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)