

Eaton 10250T15324

Catalog Number: 10250T15324

Eaton 10250T, Selector switch, 30.5 mm, Heavy-Duty, Cam 2, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Three-position, Key, Center only

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T15324
UPC	Product Length/Depth
782113297705	2.3 in
Product Height	Product Width
2 in	1.8 in
Product Weight	Warranty
0.4 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified
	UL Listed



Product specifications

Product Category

Selector switch

Throw type

60 °

Number of positions

3

Series

10250T

Type

30.5 mm, Heavy-Duty

Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

Illumination

Non-illuminated

Cam code

Cam 2

Key removal position

Center only

Actuator

Key operated

Resources

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Multimedia

[How to size and select a Power Supply](#)

Specifications and datasheets

[Eaton Specification Sheet - 10250T15324](#)

[Cam selection for pushbutton selectors](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)