

# Eaton 10250T15712-11X

Catalog Number: 10250T15712-11X

Eaton 10250T pushbutton, 10250T, Selector switch, 30.5 mm, Heavy-Duty, Cam 1, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Two-position, Key, Vertical, 2NO-2NC, Left only

## General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T15712-11X
UPC	Product Length/Depth
782113676937	1 in
Product Height	Product Width
1 in	1 in
Product Diameter	Product Weight
1.38 in	0.1 lb
Warranty	Compliances
1 year	CE Marked
Certifications	
UL Listed	
CSA Certified	



## Product specifications

### Product Category

Selector switch

### Contact configuration

2 NO-2 NC

### Throw type

60 °

### Series

10250T

### Number of positions

2

### Type

30.5 mm, Heavy-Duty

### Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

### Illumination

Non-illuminated

### Cam code

Cam 1

### Mounting method

Vertical

### Key removal position

Left only

### Actuator

Key

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250T15712-11X