

Eaton 10250T15712H620

Catalog Number: 10250T15712H620

Eaton 10250T pushbutton, Key, Chrome, Cam 1, Non-illuminated, H620, Left only, Maintained and spring return Two-position, Selector switch, NEMA 3, 3R, 4, 4X, 12, 13, 10250T, 60°

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T15712H620
UPC	Product Length/Depth
782114000380	2.5 in
Product Height	Product Width
1.75 in	1.75 in
Product Weight	Warranty
0.39 lb	1 year
Compliances	Certifications
CE Marked	UL Listed
	CSA Certified



Product specifications

Product Category

Selector switch

Throw type

60 °

Number of positions

2

Series

10250T

Type

Pushbutton

Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

Illumination

Non-illuminated

Cam code

Cam 1

Key removal position

Left only

Bezel

Chrome

Actuator

Key

Key code

H620

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Cam selection for pushbutton selectors