

# Eaton 10250T16112MD19

Catalog Number: 10250T16112MD19

10250T, 30.5 mm, Heavy-Duty, Lock with master key, Cam 1, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Two-position, Key, Left only, MD19

## General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T16112MD19
UPC	Product Length/Depth
782116996384	2.1 in
Product Height	Product Width
2.2 in	1.9 in
Product Weight	Warranty
0.4 lb	1 year
Compliances	Certifications
CE Marked	UL Listed
	CSA Certified



## Product specifications

### Throw type

60 °

### Special features

Lock with master key

### Number of positions

2

### Series

10250T

### Type

30.5 mm, Heavy-Duty

### Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

### Illumination

Non-illuminated

### Cam code

Cam 1

### Key removal position

Left only

### Actuator

Key operated

### Key code

MD19

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250T16112MD19

Cam selection for pushbutton selectors



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia