

Eaton 10250T16112MJ5

Catalog Number: 10250T16112MJ5

10250T, 30.5 mm, Heavy-Duty, Cam 1, 60° throw, NEMA 4, 4X, 13, Non-illuminated, Two-position, Key, Horizontal, Left only, MJ5

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T16112MJ5
UPC	Product Length/Depth
782116996599	2.1 in
Product Height	Product Width
2.2 in	1.9 in
Product Weight	Warranty
0.4 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified UL Listed



Product specifications

Throw type

60 °

Number of positions

2

Series

10250T

Type

30.5 mm, Heavy-Duty

Rating

NEMA 4, NEMA 4X, NEMA 13

Illumination

Non-illuminated

Cam code

Cam 1

Mounting method

Horizontal

Key removal position

Left only

Actuator

Key operated

Key code

MJ5

Resources

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Multimedia

[How to size and select a Power Supply](#)

Specifications and datasheets

[Eaton Specification Sheet - 10250T16112MJ5](#)

[Cam selection for pushbutton selectors](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)