

# Eaton 10250T16113H634

Catalog Number: 10250T16113H634

10250T, 30.5 mm, Heavy-Duty, Cam 1, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Two-position, Key, Right and left, H634

## General specifications

|                         |                      |
|-------------------------|----------------------|
| Product Name            | Catalog Number       |
| Eaton 10250T pushbutton | 10250T16113H634      |
| UPC                     | Product Length/Depth |
| 782116324422            | 2.5 in               |
| Product Height          | Product Width        |
| 1.75 in                 | 1.75 in              |
| Product Weight          | Warranty             |
| 0.39 lb                 | 1 year               |
| Compliances             | Certifications       |
| CE Marked               | UL Listed            |
|                         | CSA Certified        |



## Product specifications

### Throw type

60 °

### Number of positions

2

### Series

10250T

### Type

Pushbutton

### Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

### Illumination

Non-illuminated

### Cam code

Cam 1

### Key removal position

Right and left

### Actuator

Key

### Key code

H634

## Resources

### Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

### Multimedia

[How to size and select a Power Supply](#)

### Specifications and datasheets

[Cam selection for pushbutton selectors](#)

[Eaton Specification Sheet - 10250T16113H634](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)