

Eaton 10250T16113MD20

Catalog Number: 10250T16113MD20

10250T, 30.5 mm, Heavy-Duty, Cam 1, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Two-position, Key, Right and left, MD20

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T16113MD20
UPC	Product Length/Depth
782116324491	2.5 in
Product Height	Product Width
1.75 in	1.75 in
Product Weight	Warranty
0.39 lb	1 year
Compliances	Certifications
CE Marked	UL Listed CSA Certified



Product specifications

Throw type

60 °

Number of positions

2

Series

10250T

Type

Pushbutton

Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

Illumination

Non-illuminated

Cam code

Cam 1

Key removal position

Right and left

Actuator

Key

Key code

MD20

Resources

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Multimedia

[How to size and select a Power Supply](#)

Specifications and datasheets

[Eaton Specification Sheet - 10250T16113MD20](#)

[Cam selection for pushbutton selectors](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)