

Eaton 10250T181HLP

Catalog Number: 10250T181HLP

Eaton 10250T pushbutton, Class I Division 2 Indicating Light, Watertight and Oiltight, Standard actuator, LED, Transformer, NEMA 3, 3R, 3S, 4, 4X, 12, 13, NEC Class I Division 2, Groups B, C and D, Blue, Plastic, 120 V

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T181HLP
UPC	Product Length/Depth
782114516379	0.01 in
Product Height	Product Width
0.01 in	0.01 in
Product Weight	Warranty
0.01 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified
	UL Listed



Product specifications

Light unit type

LED, transformer

Series

10250T

Type

30.5 mm, Class I Division 2 Watertight/Oiltight

Light unit voltage

120 Vac

Rating

NEMA 12

NEMA 3

NEMA 3R

NEC Class I Division 2, Groups B, C and D

NEMA 4

NEMA 4X

NEMA 3S

NEMA 13

Lens material

Plastic

Lens color

Blue

Actuator

Standard

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T181HLP



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia