

Eaton 10250T182H

Catalog Number: 10250T182H

Eaton 10250T pushbutton, Class I Division 2 Indicating Light, Watertight and Oiltight, Standard actuator, Incandescent, Transformer, NEMA 3, 3R, 3S, 4, 4X, 12, 13, NEC Class I Division 2, Groups B, C and D, 240 V

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T182H
UPC	Product Length/Depth
782114510889	0.01 in
Product Height	Product Width
0.01 in	0.01 in
Product Weight	Warranty
0.01 lb	1 year
Compliances	Certifications
CE Marked	UL Listed
	CSA Certified



Product specifications

Light unit type

Incandescent, transformer

Series

10250T

Type

30.5 mm, Class I Division 2 Watertight/Oiltight

Light unit voltage

240 Vac

Rating

NEMA 3

NEMA 3R

NEMA 13

NEMA 12

NEMA 4X

NEMA 3S

NEC Class I Division 2, Groups B, C and D

NEMA 4

Actuator

Standard

Resources

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Multimedia

[How to size and select a Power Supply](#)

Specifications and datasheets

[Eaton Specification Sheet - 10250T182H](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)