

Eaton 10250T183HLRP06

Catalog Number: 10250T183HLRP06

Eaton 10250T pushbutton, Class I Division 2 Indicating Light, Watertight and Oiltight, Standard actuator, LED, Transformer, NEMA 3, 3R, 3S, 4, 4X, 12, 13, NEC, Groups B, C and D, Red, Plastic, 380 V

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T183HLRP06
UPC	Product Length/Depth
782114540435	0.01 in
Product Height	Product Width
0.01 in	0.01 in
Product Weight	Warranty
0.01 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified
	UL Listed



Product specifications

Light unit type

LED, transformer

Series

10250T

Type

30.5 mm, Class I Division 2 Watertight/Oiltight

Light unit voltage

380 Vac

Rating

NEC Class I Division 2, Groups B, C and D

NEMA 3S

NEMA 13

NEMA 3R

NEMA 4X

NEMA 3

NEMA 12

NEMA 4

Lens material

Plastic

Lens color

Red

Actuator

Standard

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T183HLRP06



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia