

Eaton 10250T197HLAG2A

Catalog Number: 10250T197HLAG2A

Eaton 10250T pushbutton, Class I Division 2 Indicating Lights Watertight and Oiltight, Standard actuator, LED, Full voltage, NEMA 3, 3R, 3S, 4, 4X, 12, 13, NEC Class I Division 2, Groups B, C and D, Amber, Glass, 24 Vac/dc

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T197HLAG2A
UPC	Product Length/Depth
782114541418	0.01 in
Product Height	Product Width
0.01 in	0.01 in
Product Weight	Warranty
0.01 lb	1 year
Compliances	Certifications
CE Marked	UL Listed
	CSA Certified



Product specifications

Light unit type

LED, full voltage

Series

10250T

Type

30.5 mm, Class I Division 2 Watertight/Oiltight

Light unit voltage

24 Vac/dc

Rating

NEMA 3R

NEMA 4

NEC Class I Division 2, Groups B, C and D

NEMA 12

NEMA 3

NEMA 13

NEMA 4X

NEMA 3S

Lens material

Glass

Lens color

Amber

Actuator

Standard

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T197HLAG2A



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia