

# Eaton 10250T197LGG12

Catalog Number: 10250T197LGG12

Eaton 10250T pushbutton, Heavy-duty watertight and oiltight Indicating Light, Standard actuator, LED, Full voltage, NEMA 3, 3R, 4, 4X, 12, 13, Green, Glass, 12 Vac/dc

## General specifications

|                         |                      |
|-------------------------|----------------------|
| Product Name            | Catalog Number       |
| Eaton 10250T pushbutton | 10250T197LGG12       |
| UPC                     | Product Length/Depth |
| 782114710777            | 0.01 in              |
| Product Height          | Product Width        |
| 0.01 in                 | 0.01 in              |
| Product Weight          | Warranty             |
| 0.01 lb                 | 1 year               |
| Compliances             | Certifications       |
| CE Marked               | UL Listed            |
|                         | CSA Certified        |



## Product specifications

### Light unit type

LED, full voltage

### Series

10250T

### Type

30.5 mm, Heavy-Duty Watertight/Oiltight

### Light unit voltage

12 Vac/dc

### Rating

NEMA 3

NEMA 13

NEMA 12

NEMA 4X

NEMA 4

NEMA 3R

### Lens material

Glass

### Lens color

Green

### Actuator

Standard

## Resources

### Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

### Multimedia

[How to size and select a Power Supply](#)

### Specifications and datasheets

[Eaton Specification Sheet - 10250T197LGG12](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)