

Eaton 10250T197LRG24

Catalog Number: 10250T197LRG24

Eaton 10250T pushbutton, Heavy-duty watertight and oiltight Indicating Light, Standard actuator, LED, Full voltage, NEMA 3, 3R, 4, 4X, 12, 13, Red, Glass, 24 Vac/dc

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T197LRG24
UPC	Product Length/Depth
782114710876	0.01 in
Product Height	Product Width
0.01 in	0.01 in
Product Weight	Warranty
0.01 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified
	UL Listed



Product specifications

Light unit type

LED, full voltage

Series

10250T

Type

30.5 mm, Heavy-Duty Watertight/Oiltight

Light unit voltage

24 Vac/dc

Rating

NEMA 4X

NEMA 3R

NEMA 12

NEMA 4

NEMA 3

NEMA 13

Lens material

Glass

Lens color

Red

Actuator

Standard

Resources

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Multimedia

[How to size and select a Power Supply](#)

Specifications and datasheets

[Eaton Specification Sheet - 10250T197LRG24](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)