

Eaton 10250T197LRP60

Catalog Number: 10250T197LRP60

Eaton 10250T pushbutton, Heavy-duty watertight and oiltight Indicating Light, Standard actuator, LED, Full voltage, NEMA 3, 3R, 4, 4X, 12, 13, Red, Plastic, 60 Vac/dc

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T197LRP60
UPC	Product Length/Depth
782114711033	0.01 in
Product Height	Product Width
0.01 in	0.01 in
Product Weight	Warranty
0.01 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified UL Listed

Product specifications

Light unit type

LED, full voltage

Series

10250T

Type

30.5 mm, Heavy-Duty Watertight/Oiltight

Light unit voltage

60 Vac/dc

Rating

NEMA 3

NEMA 12

NEMA 13

NEMA 4X

NEMA 3R

NEMA 4

Lens material

Plastic

Lens color

Red

Actuator

Standard

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T197LRP60



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia