

Eaton 10250T201NC1NX

Catalog Number: 10250T201NC1NX

Eaton 10250T pushbutton, Heavy-Duty Assembled Indicating Light, Standard actuator, Incandescent, Resistor, NEMA 3, 3R, 3S, 4, 4X, 12, 13, 120MB, Red, Plastic, 120 Vac/dc

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T201NC1NX
UPC	Product Length/Depth
782113370934	0.01 in
Product Height	Product Width
0.01 in	0.01 in
Product Weight	Warranty
0.01 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified UL Listed
Catalog Notes	
Parts assembled at factory	



Product specifications

LED lamp number

120MB

Supply voltage

120 Vac/dc

Light unit type

Incandescent, resistor

Series

10250T

Type

30.5 mm, Heavy-Duty Watertight/Oiltight

Rating

NEMA 13

NEMA 4

NEMA 3

NEMA 3R

NEMA 4X

NEMA 3S

NEMA 12

Lens material

Plastic

Lens color

Red

Actuator

Standard

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T201NC1NX



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia