

Eaton 10250T201NC2NX

Catalog Number: 10250T201NC2NX

Eaton 10250T pushbutton, Heavy-Duty Assembled Indicating Light, Standard actuator, Incandescent, Resistor, NEMA 3, 3R, 3S, 4, 4X, 12, 13, 120MB, Green, Plastic, 120 Vac/dc

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T201NC2NX
UPC	Product Length/Depth
782113370958	0.01 in
Product Height	Product Width
0.01 in	0.01 in
Product Weight	Warranty
0.01 lb	1 year
Compliances	Certifications
CE Marked	UL Listed CSA Certified
Catalog Notes	
Parts assembled at factory	



Product specifications

LED lamp number

120MB

Supply voltage

120 Vac/dc

Light unit type

Incandescent, resistor

Series

10250T

Type

30.5 mm, Heavy-Duty Watertight/Oiltight

Rating

NEMA 4

NEMA 12

NEMA 4X

NEMA 13

NEMA 3S

NEMA 3

NEMA 3R

Lens material

Plastic

Lens color

Green

Actuator

Standard

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T201NC2NX



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia