

# Eaton 10250T206HWG

Catalog Number: 10250T206HWG

Eaton 10250T pushbutton, Class I Division 2 Indicating Light, Watertight and Oiltight, Standard actuator, Incandescent, Full voltage, NEMA 3, 3R, 3S, 4, 4X, 12, 13, NEC Class I Division 2, Groups B, C and D, White, Glass, 24 Vac/dc

## General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T206HWG
UPC	Product Length/Depth
782114517499	0.01 in
Product Height	Product Width
0.01 in	0.01 in
Product Weight	Warranty
0.01 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified
	UL Listed

## Product specifications

### Light unit type

Incandescent, full voltage

### Series

10250T

### Type

30.5 mm, Class I Division 2 Watertight/Oiltight

### Light unit voltage

24 Vac/dc

### Rating

NEMA 3R

NEMA 4X

NEMA 4

NEMA 12

NEMA 3S

NEMA 3

NEMA 13

NEC Class I Division 2, Groups B, C and D

### Lens material

Glass

### Lens color

White

### Actuator

Standard

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250T206HWG



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia