

Eaton 10250T206NC7NX

Catalog Number: 10250T206NC7NX

Eaton 10250T pushbutton, Heavy-Duty Assembled Indicating Light, Standard actuator, Incandescent, Full voltage, NEMA 3, 3R, 3S, 4, 4X, 12, 13, 24 Vac/dc, #757, Red, Glass, 24 Vac/dc

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T206NC7NX
UPC	Product Length/Depth
782113747934	0.01 in
Product Height	Product Width
0.01 in	0.01 in
Product Weight	Warranty
0.01 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified UL Listed
Catalog Notes	
Parts assembled at factory	



Product specifications

LED lamp number

#757

Supply voltage

24 Vac/dc

Light unit type

Incandescent, full voltage

Series

10250T

Type

30.5 mm, Heavy-Duty Watertight/Oiltight

Lamp voltage

24 Vac/dc

Rating

NEMA 3

NEMA 3S

NEMA 13

NEMA 4

NEMA 3R

NEMA 4X

NEMA 12

Lens material

Glass

Lens color

Red

Actuator

Standard

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T206NC7NX