

Eaton 10250T20LL

Catalog Number: 10250T20LL

Eaton 10250T pushbutton, 10250T, 30.5 mm, Heavy-Duty, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Two-position, Lever, Blue actuator, 1NO-1NC

General specifications

| | |
|-------------------------|----------------------|
| Product Name | Catalog Number |
| Eaton 10250T pushbutton | 10250T20LL |
| UPC | Product Length/Depth |
| 782113357379 | 1 in |
| Product Height | Product Width |
| 1 in | 1 in |
| Product Diameter | Product Weight |
| 1.38 in | 0.1 lb |
| Warranty | Compliances |
| 1 year | CE Marked |
| Certifications | |
| UL Listed | |
| CSA Certified | |



Product specifications

Contact configuration

1 NO-1 NC

Throw type

60 °

Series

10250T

Number of positions

2

Type

30.5 mm, Heavy-Duty

Actuator color

Blue

Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

Illumination

Non-illuminated

Actuator

Lever

Resources

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Multimedia

[How to size and select a Power Supply](#)

Specifications and datasheets

[Eaton Specification Sheet - 10250T20LL](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)