

Eaton 10250T224LGG06

Catalog Number: 10250T224LGG06

Eaton 10250T pushbutton, Heavy-duty watertight and oiltight Indicating Light, PresTest, LED, Transformer, NEMA 3, 3R, 4, 4X, 12, 13, Green, Glass, 480 V

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T224LGG06
UPC	Product Length/Depth
782114713136	0.01 in
Product Height	Product Width
0.01 in	0.01 in
Product Weight	Warranty
0.01 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified
	UL Listed



Product specifications

Light unit type

LED, transformer

Series

10250T

Type

30.5 mm, Heavy-Duty Watertight/Oiltight

Light unit voltage

480 Vac

Rating

NEMA 4

NEMA 3

NEMA 13

NEMA 12

NEMA 3R

NEMA 4X

Lens material

Glass

Lens color

Green

Actuator

PresTest

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T224LGG06



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia