

Eaton 10250T22KB

Catalog Number: 10250T22KB

Eaton 10250T pushbutton, Heavy-Duty Assembled Selector Switch, 10250T, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Three-position, Knob, Black actuator, 2NO-2NC

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T22KB
UPC	Product Length/Depth
782113358260	2.6 in
Product Height	Product Width
4.7 in	2.2 in
Product Weight	Warranty
0.35 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified
	UL Listed



Product specifications

Contact configuration

2 NO-2 NC

Throw type

60 °

Series

10250T

Number of positions

3

Type

30.5 mm, Heavy-Duty

Actuator color

Black

NEMA rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

Illumination

Non-illuminated

Size

30.5 mm

Actuator

Knob

Resources

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Multimedia

[How to size and select a Power Supply](#)

Specifications and datasheets

[Eaton Specification Sheet - 10250T22KB](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)