

Eaton 10250T235NC24X

Catalog Number: 10250T235NC24X

Eaton 10250T pushbutton, Heavy-Duty Assembled Indicating Light, PresTest, Incandescent, Full voltage, NEMA 3, 3R, 4, 4X, 12, 13, 24 Vac/dc, #757, Blue, Plastic, 24 Vac/dc

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T235NC24X
UPC	Product Length/Depth
782114272442	0.01 in
Product Height	Product Width
0.01 in	0.01 in
Product Weight	Warranty
0.01 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified UL Listed
Catalog Notes	
Parts assembled at factory	



Product specifications

LED lamp number

#757

Supply voltage

24 Vac/dc

Light unit type

Incandescent, full voltage

Series

10250T

Type

30.5 mm, Heavy-Duty Watertight/Oiltight

Lamp voltage

24 Vac/dc

Rating

NEMA 3

NEMA 13

NEMA 4

NEMA 12

NEMA 3R

NEMA 4X

Lens material

Plastic

Lens color

Blue

Actuator

PresTest

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T235NC24X