

Eaton 10250T3011-2X

Catalog Number: 10250T3011-2X

Eaton 10250T pushbutton, 10250T, 30.5 mm, Metal, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Two-position, Lever, Black actuator, 2NO, Chrome bezel

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T3011-2X
UPC	Product Length/Depth
782113651606	1 in
Product Height	Product Width
1 in	1 in
Product Diameter	Product Weight
1.38 in	0.1 lb
Warranty	Compliances
1 year	CE Marked
Certifications	Catalog Notes
CSA Certified UL Listed	Field convertible to Horizontal Mounting or order operator only and separate operator cap. Assembled at Factory

Product specifications

Contact configuration

2 NO

Throw type

60 °

Series

10250T

Number of positions

2

Type

30.5 mm, metallic

Actuator color

Black

Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

Illumination

Non-illuminated

Bezel

Chrome

Actuator

Lever

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T3011-2X



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia