

Eaton 10250T37NRF

Catalog Number: 10250T37NRF

Eaton 10250T pushbutton, Heavy-duty watertight and oiltight Indicating Light, Flashing lamp, PresTest, Incandescent, Transformer, NEMA 3, 3R, 4, 4X, 12, 13, Red, Plastic, 120 V

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T37NRF
UPC	Product Length/Depth
782113781907	0.01 in
Product Height	Product Width
0.01 in	0.01 in
Product Weight	Warranty
0.01 lb	1 year
Compliances	Certifications
CE Marked	UL Listed
	CSA Certified



Product specifications

Special features

Flashing lamp

Light unit type

Incandescent, transformer

Series

10250T

Type

30.5 mm, Heavy-Duty Watertight/Oiltight

Light unit voltage

120 Vac

Rating

NEMA 12

NEMA 4

NEMA 3

NEMA 3R

NEMA 4X

NEMA 13

Lens material

Plastic

Lens color

Red

Actuator

PresTest

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T37NRF



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia