

Eaton 10250T397LAD2A

Catalog Number: 10250T397LAD2A

Eaton 10250T pushbutton, 30.5 mm, Heavy-Duty, 40 mm, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, Momentary, Amber actuator, LED, full voltage light unit, Flush, 120 V light unit, Chrome bezel, Bayonet base, 120 V lamp, Plastic actuator

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T397LAD2A
UPC	Product Length/Depth
782114753729	1.63 in
Product Height	Product Width
1.78 in	1.59 in
Product Weight	Warranty
0.01 lb	1 year
Compliances	Certifications
CE Marked	UL Listed CSA Certified

Catalog Notes

Unit does not include lamp. Order LED separately to match lens.



Product specifications

Special features

10250T series

Actuator color

Amber

Actuator material

Plastic

Light unit voltage

120 Vac

Lamp voltage - min

120 VAC

Rating

NEMA 12

NEMA 3

NEMA 4X

NEMA 4

NEMA 13

NEMA 3R

Size

40 mm

Mounting method

Flush

Bezel

Chrome

LED lamp number

Bayonet base

Series

10250T

Lamp voltage - max

120 VAC

Light unit type

LED, full voltage

Type

30.5 mm Heavy-Duty Watertight/Oiltight

Operating mode

Momentary

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T397LAD2A

Illumination

Illuminated

Application

Pushbutton



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)