

Eaton 10250T397LAD74-2

Catalog Number: 10250T397LAD74-2

Eaton 10250T, 30.5 mm, Heavy-Duty, 40 mm, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, Momentary, Amber actuator, LED, full voltage light unit, Flush, 2NO, 74 Vac/dc light unit, Chrome bezel, Bayonet base, 74 Vac/dc lamp, Plastic actuator

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T397LAD74-2
UPC	Product Length/Depth
782116077441	1.63 in
Product Height	Product Width
1.78 in	1.59 in
Product Weight	Warranty
0.01 lb	1 year
Compliances	Certifications
CE Marked	UL Listed CSA Certified



Product specifications

Contact configuration

2 NO

Actuator color

Amber

Actuator material

Plastic

Light unit voltage

74 Vac/dc

Lamp voltage - min

74 V

Rating

NEMA 3

NEMA 4

NEMA 13

NEMA 3R

NEMA 4X

NEMA 12

Size

40 mm

Mounting method

Flush

Bezel

Chrome

LED lamp number

Bayonet base

Series

10250T

Lamp voltage - max

74 V

Light unit type

LED, full voltage

Type

30.5 mm, Heavy-Duty

Operating mode

Momentary

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T397LAD74-2

Illumination

Illuminated



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)