

# Eaton 10250T397LRD24

Catalog Number: 10250T397LRD24

Eaton 10250T pushbutton, 30.5 mm, Heavy-Duty, 40 mm, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, Momentary, Red actuator, LED, full voltage light unit, Flush, 24 Vac/dc light unit, Chrome bezel, Bayonet base, 24 Vac/dc lamp, Plastic actuator

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton 10250T pushbutton	10250T397LRD24
<b>UPC</b>	<b>Product Length/Depth</b>
782114754078	1.63 in
<b>Product Height</b>	<b>Product Width</b>
1.78 in	1.59 in
<b>Product Weight</b>	<b>Warranty</b>
0.01 lb	1 year
<b>Compliances</b>	<b>Certifications</b>
CE Marked	CSA Certified UL Listed

## Catalog Notes

Unit does not include lamp. Order LED separately to match lens.



## Product specifications

### Special features

10250T series

### Actuator color

Red

### Actuator material

Plastic

### Light unit voltage

24 Vac/dc

### Lamp voltage - min

24 V

### Rating

NEMA 12

NEMA 4X

NEMA 4

NEMA 13

NEMA 3

NEMA 3R

### Size

40 mm

### Mounting method

Flush

### Bezel

Chrome

### LED lamp number

Bayonet base

### Series

10250T

### Lamp voltage - max

24 V

### Light unit type

LED, full voltage

### Type

30.5 mm Heavy-Duty Watertight/Oiltight

### Operating mode

Momentary

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250T397LRD24

Illumination

Illuminated

Application

Pushbutton



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)