

# Eaton 10250T397LYD24

Catalog Number: 10250T397LYD24

Eaton 10250T pushbutton, 30.5 mm, Heavy-Duty, 40 mm, NEMA 3, 3R, 4, 4X, 12, 13, Illuminated, Momentary, Yellow actuator, LED, full voltage light unit, Flush, 24 Vac/dc light unit, Chrome bezel, Bayonet base, 24 Vac/dc lamp, Plastic actuator

## General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T397LYD24
UPC	Product Length/Depth
782114754337	1.63 in
Product Height	Product Width
1.78 in	1.59 in
Product Weight	Warranty
0.01 lb	1 year
Compliances	Certifications
CE Marked	CSA Certified
	UL Listed

## Catalog Notes

Unit does not include lamp. Order LED separately to match lens.



## Product specifications

### Special features

10250T series

### Actuator color

Yellow

### Actuator material

Plastic

### Light unit voltage

24 Vac/dc

### Lamp voltage - min

24 V

### Rating

NEMA 3

NEMA 3R

NEMA 4X

NEMA 4

NEMA 13

NEMA 12

### Size

40 mm

### Mounting method

Flush

### Bezel

Chrome

### LED lamp number

Bayonet base

### Series

10250T

### Lamp voltage - max

24 V

### Light unit type

LED, full voltage

### Type

30.5 mm Heavy-Duty Watertight/Oiltight

### Operating mode

Momentary

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250T397LYD24

Illumination

Illuminated

Application

Pushbutton



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)