

Eaton 10250T4022LL-1111X

Catalog Number: 10250T4022LL-1111X

Eaton 10250T pushbutton, 10250T, 30.5 mm, Heavy-Duty, Cam 2, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Three-position, Maintained, Lever, Blue actuator, 4NO-2NC

General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T4022LL-1111X
UPC	Product Length/Depth
786685106038	1.9 in
Product Height	Product Width
2.1 in	1.9 in
Product Weight	Warranty
0.2 lb	1 year
Compliances	Certifications
CE Marked	UL Listed
	CSA Certified



Product specifications

Contact configuration

4 NO-2 NC

Throw type

60 °

Number of positions

3

Actuator color

Blue

Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

Size

30.5 mm

Series

10250T

Type

30.5 mm, Heavy-Duty

Operating mode

Maintained

NEMA rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

Illumination

Non-illuminated

Cam code

Cam 2

Actuator

Lever

Resources

Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

Multimedia

How to size and select a Power Supply

Specifications and datasheets

Eaton Specification Sheet - 10250T4022LL-1111X



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)