

# Eaton 10250T4023LO-3X

Catalog Number: 10250T4023LO-3X

Eaton 10250T pushbutton, 10250T, 30.5 mm, Metal, 60° throw, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Three-position, Lever, Orange actuator, 2NC

## General specifications

Product Name	Catalog Number
Eaton 10250T pushbutton	10250T4023LO-3X
UPC	Product Length/Depth
786685106052	2.2 in
Product Height	Product Width
1.9 in	1.9 in
Product Weight	Warranty
0.25 lb	1 year
Compliances	Certifications
CE Marked	UL Listed
	CSA Certified



## Product specifications

### Product Category

Selector switch

### Contact configuration

2 NC

### Throw type

60 °, left/center/right

### Number of positions

3

### Actuator color

Orange

### Rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

### Size

30.5 mm

### Enclosure

NEMA 4X

NEMA 4

NEMA 3

NEMA 13

NEMA 12

NEMA 3R

### Bezel

Zinc die cast, chrome

### Series

10250T

### Type

30.5 mm, metallic

### Operating mode

Maintained

### NEMA rating

NEMA 3, NEMA 3R, NEMA 4, NEMA 4X, NEMA 12, NEMA 13

### Illumination

Non-illuminated

### Cam code

Cam 3

### Actuator

## Resources

### Catalogs

Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions

### Multimedia

How to size and select a Power Supply

### Specifications and datasheets

Eaton Specification Sheet - 10250T4023LO-3X



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)